

HOLEX

ET collet with radial compensation for tapping and reaming, ET 40, Nominal clamping \varnothing d: 8 mm



Order data

Order number	309449 8
GTIN	4045197783240
Item class	32Z

Description

Version:

Hardened and ground.

Advantage:

The radial compensation allows correction of slight **centring errors** (for the required concentricity and thread or fit quality). Axial compensation of 0.1 mm.

Application:

For tapping and reaming on milling and turning centres.

Suitable for :

All standard ER collet chucks.

Note:

Clamps only the nominal \varnothing . **Not compatible with the CENTRO P precision ER collet chuck.**

Standard: Manufacturer's standard

Radial compensation R reaming: 0.1 mm

Technical description

Nominal clamping \varnothing d	8 mm
Adapter	ET 40
Standard	Manufacturer's standard

External \varnothing D	41 mm
Overall length L	49 mm
Axial compensation	0.2 mm
Radial compensation R thread tapping	0.5 mm
Radial compensation R reaming	0.1 mm
Type of product	Clamping head