



ET collet with radial compensation for tapping and reaming, ET 40, Nominal clamping \varnothing d: 11 mm



Order data

| | |
|--------------|---------------|
| Order number | 309449 11 |
| GTIN | 4045197783271 |
| Item class | 32Z |

Description

Version:

Hardened and ground.

Advantage:

The radial compensation allows correction of slight **centring errors** (for the required concentricity and thread or fit quality). Axial compensation of 0.1 mm.

Application:

For tapping and reaming on milling and turning centres.

Suitable for :

All standard ER collet chucks.

Note:

Clamps only the nominal \varnothing . **Not compatible with the CENTRO P precision ER collet chuck.**

Standard: Manufacturer's standard

Radial compensation R reaming: 0.1 mm

Technical description

| | |
|----------------------------------|-------------------------|
| Nominal clamping \varnothing d | 11 mm |
| Adapter | ET 40 |
| Standard | Manufacturer's standard |

| | |
|--------------------------------------|---------------|
| External Ø D | 41 mm |
| Overall length L | 49 mm |
| Axial compensation | 0.2 mm |
| Radial compensation R thread tapping | 0.5 mm |
| Radial compensation R reaming | 0.1 mm |
| Type of product | Clamping head |