

**HOLEX****ET collet with radial compensation for tapping and reaming, ET 32, Nominal clamping  $\varnothing$  d: 7mm****Order data**

Order number	309448 7
GTIN	4045197783127
Item class	32Z

**Description****Version:**

Hardened and ground.

**Advantage:**

The radial compensation allows correction of slight **centring errors** (for the required concentricity and thread or fit quality). Axial compensation of 0.1 mm.

**Application:**

For tapping and reaming on milling and turning centres.

**Suitable for:**

All standard ER collet chucks.

**Note:**

Clamps only the nominal  $\varnothing$ . **Not compatible with the CENTRO P precision ER collet chuck.**

**Technical description**

Nominal clamping $\varnothing$ d	7 mm
Adapter	ET 32
Standard	Manufacturer's standard
External $\varnothing$ D	33 mm

Overall length L	42.5 mm
Axial compensation	0.1 mm
Radial compensation R thread tapping	0.5 mm
Radial compensation R reaming	0.1 mm
Type of product	Collet