

HOLEX**ET collet with radial compensation for tapping and reaming, ET 25, Nominal clamping \varnothing d: 9mm****Order data**

Order number	309447 9
GTIN	4045197783066
Item class	32Z

Description**Version:**

Hardened and ground.

Advantage:

The radial compensation allows correction of slight **centring errors** (for the required concentricity and thread or fit quality). Axial compensation of 0.1 mm.

Application:

For tapping and reaming on milling and turning centres.

Suitable for:

All standard ER collet chucks.

Note:

Clamps only the nominal \varnothing . **Not compatible with the CENTRO P precision ER collet chuck.**

Technical description

Nominal clamping \varnothing d	9 mm
Adapter	ET 25
Standard	Manufacturer's standard
External \varnothing D	26 mm

Overall length L	35 mm
Axial compensation	0.1 mm
Radial compensation R thread tapping	0.4 mm
Radial compensation R reaming	0.05 mm
Type of product	Collet