

HOLEX®

ET collet with radial compensation for tapping and reaming, ET 40, Nominal clamping \varnothing d: 7 mm

Order data

Order number	309449 7
GTIN	4045197783233
Item class	32Z

Description

Version:

Hardened and ground.

Advantage:

The radial compensation allows correction of slight **centring errors** (for the required concentricity and thread or fit quality). Axial compensation of 0.1 mm.

Application:

For tapping and reaming on milling and turning centres.

Suitable for :

All standard ER collet chucks.

Note:

Clamps only the nominal \varnothing . **Not compatible with the CENTRO P precision ER collet chuck.**

Norm: Manufacturer's standard

External \varnothing D: 41 mm

Overall length L: 49 mm

Axial compensation: 0.2 mm

Radial compensation R thread tapping: 0.5 mm

Radial compensation R reaming: 0.1 mm

Technical description

External \varnothing D	41 mm
Adapter	ET 40
Axial range	mm
Norm	Manufacturer's standard
Axial compensation	0.2 mm
Type	

Overall length L	49 mm
Concentricity	μm
Radial compensation R thread tapping	0.5 mm
Radial compensation R reaming	0.1 mm
Type of product	