



## High feed rate milling cutter MFH mini, with thread, $\varnothing D$ / number of teeth Z: 35/6mm



### Order data

Order number	221960 35/6
GTIN	2050001929952
Item class	250

### Technical description

Mounting thread M	M16
Cutting edge $\varnothing D_c$	35 mm
Number of cutting edges Z	6
suitable indexable insert	LOGU 0303..
Overall length $L_{tot}$	40 mm
Insert screw	229713 (8IP; 1.2 Nm)
$\varnothing D_3$	28 mm
maximum cutting depth $a_{p,max}$	1 mm
Through-coolant	yes
Ramping length L for $\alpha_{max}$	26.3 mm
Circular interpolation milling $\varnothing D_{min}$	63 mm
Ramping angle $\alpha_{max}$	0.65 degrees
Circular interpolation milling $\varnothing D_{max}$	68 mm
Shank type	with thread

Milling application	Circular milling
Milling application	Ramping
Milling application	Plunging
Machining strategy	HPC
Type of product	Copy mill

---

## Accessories

Clamping screw	229713
----------------	--------