

Garant

**Hi5 high feed rate indexable face mill, with bore, Ø D / number of teeth Z:
40/4mm**


Order data

Order number	213210 40/4
GTIN	4045197783547
Item class	210

Description
Version:

Particularly smooth-running, due to unequal spacing of the teeth.

Note:

Use GARANT torque screwdriver TQ No. **211750 size 2.2** with bit No. **674252 size 10IP**.

Technical description

Ø D ₃	25.6 mm
Overall length L _{tot}	40 mm
suitable indexable insert	POMX 0704..
maximum cutting depth a _{p max}	1.4 mm
Pack of insert screws	219884 (10IP; 2.2 Nm)
Number of cutting edges Z	4
Mounting bore Ø	16 mm
Cutting edge Ø D _c	40 mm

Through-coolant	yes
Series	Hi5
Setting angle κ	90 degrees
Shank type	with bore
Spacing of the cutters	unequal spacing
Tool exchange	PowerCard
Type of product	Copy mill

Accessories

PrecisionBit for Torx Plus®, 1/4 inch E 6.3 Torx Plus® profile 10IP	674252 10IP
Torque screwdriver, fixed setting set torque 2,2 N·m	211750 2,2
Set of insert screws 10 pieces	219884