

**Garant**

**Hi5 high feed rate indexable face mill, with bore, Ø D / number of teeth Z:  
50/5mm**


**Order data**

Order number	213210 50/5
GTIN	4045197783554
Item class	210

**Description**
**Version:**

Particularly smooth-running, due to unequal spacing of the teeth.

**Note:**

Use GARANT torque screwdriver TQ No. **211750 size 2.2** with bit No. **674252 size 10IP**.

**Technical description**

Ø D <sub>3</sub>	35.6 mm
maximum cutting depth a <sub>p,max</sub>	1.4 mm
Overall length L <sub>tot</sub>	40 mm
Pack of insert screws	219884 (10IP; 2.2 Nm)
Mounting bore Ø	22 mm
suitable indexable insert	POMX 0704..
Number of cutting edges Z	5

Cutting edge $\varnothing D_c$	50 mm
Through-coolant	yes
Series	Hi5
Setting angle $\kappa$	90 degrees
Shank type	with bore
Spacing of the cutters	unequal spacing
Tool exchange	PowerCard
Type of product	Copy mill

---

## Accessories

PrecisionBit for Torx Plus®, 1/4 inch E 6.3 Torx Plus® profile 10IP	674252 10IP
Set of insert screws 10 pieces	219884
Torque screwdriver, fixed setting set torque 2,2 N·m	211750 2,2