

Garant

**Hi5 high feed rate indexable face mill, with bore, Ø D / number of teeth Z:
50/5mm**


Order data

Order number	213210 50/5
GTIN	4045197783554
Item class	210

Description
Version:

Particularly smooth-running, due to unequal spacing of the teeth.

Note:

Use GARANT torque screwdriver TQ No. **211750 size 2.2** with bit No. **674252 size 10IP**.

Tool exchange: PowerCard

Through-coolant: yes

Number of cutting edges Z: 5

Ø D₃: 35.6 mm

maximum cutting depth a_{p,max}: 1.4 mm

Overall length L_{tot}: 40 mm

Mounting bore Ø: 22 mm

suitable indexable insert: POMX 0704..

Technical description

Ø D ₃	35.6 mm
maximum cutting depth a _{p,max}	1.4 mm

Overall length L_{tot}	40 mm
Pack of insert screws	219884 (10IP; 2.2 Nm)
Mounting bore \varnothing	22 mm
suitable indexable insert	POMX 0704..
Number of cutting edges Z	5
Cutting edge $\varnothing D_c$	50 mm
Through-coolant	yes
Series	Hi5
Setting angle κ	90 °
Shank type	with bore
Spacing of the cutters	unequal spacing
Tool exchange	PowerCard
Type of product	Copy mill

Accessories

PrecisionBit for Torx Plus®, 1/4 inch E 6.3 Torx Plus® profile 10IP	674252 10IP
Set of insert screws 10 pieces	219884
Torque screwdriver, fixed setting set torque 2,2 N·m	211750 2,2