



Set of bits BiTorsion 30 pieces, diamond-coated



Order data

Order number	675797
GTIN	4013288179814
Item class	63H

Description

Content:

Bits C 6.3 (1/4 inch) set; 1 coupling shank.

Content:

Bits, length 25 mm, C 6.3, for Phillips: No. 675510 2 pcs. size 1/25; 4 pcs. size 2/25; 1 pc. size 3/25

Bits, length 25 mm, C 6.3, for Pozidriv: No. 675530 2 pcs. size 1/25; 4 pcs. size 2/25; 1 pc. size 3/25

Bits, length 25 mm, C 6.3, for slot-head: 1 pc. each size 0.8x5.5; 1.0x5.5; 1.2x6.5

Bits, length 25 mm, C 6.3, for internal Torx®: Similar to No. 675550 2 pcs. size TX10; 2 pcs. size

TX15; 3 pcs. size TX20; 3 pcs. size TX25; 1 pc. size TX30; 1 pc. TX40

"Rapidaptor" adaptor: 1 pc. No. 675020 size 6.3K

Technical description

Drive profile	Pozidriv screwdriver
Drive profile	Slot-head screwdriver
Drive profile	Screwdriver for TORX® screws
Drive profile	Screwdriver for Phillips
Manufacturer's designation	Bit-Check 30 Diamond 1
Number of pieces	30

Bit length	25 mm
Type of product	Bit tool

Accessories

Bit for Pozidriv, 1/4 inch BiTorsion, diamond-coated Cross-head size / overall length 2/25 mm	675530 2/25
Shank with magnet / quick-change coupling Hexagon shank 6,3K	675020 6,3K
Bit for Pozidriv, 1/4 inch BiTorsion, diamond-coated Cross-head size / overall length 3/25 mm	675530 3/25
Bit for Pozidriv, 1/4 inch BiTorsion, diamond-coated Cross-head size / overall length 1/25 mm	675530 1/25
Bit for Phillips, 1/4 inch BiTorsion diamond-coated Cross-head size / overall length 3/25 mm	675510 3/25
Bit for Phillips, 1/4 inch BiTorsion diamond-coated Cross-head size / overall length 2/25 mm	675510 2/25
Bit for Phillips, 1/4 inch BiTorsion diamond-coated Cross-head size / overall length 1/25 mm	675510 1/25