

Ansell**Pair of chemical protective gloves AlphaTec® 58-435, Glove size: 8****Order data**

Order number	094757 8
GTIN	10076490470934
Item class	04P

Description**Version:**

Category III safety gloves.

Alphatec® 58-435. Safety gloves of nitrile material without backing, with an inner lining of cotton velour. High flexibility and high freedom of movement for fingers. The close fit guarantees a secure fit on the palm. The high-performance nitrile coating provides a longer period of wearing an outstanding protection against split skin, puncture wounds and abrasions. The long gauntlet provides an insuperable barrier preventing droplets striking the forearm. The extended gauntlet extends protection right up to the forearm.

Note:

The minimum order quantity corresponds to one pack unit quantity (VPE) or a multiple thereof.
EN 374:2016: Type A (AJKLOPT)

Technical description

Glove size	8
Series	AlphaTec®
Type of glove	Chemicals protection gloves

Protection category	Category III
Contents	12
Glove characteristics	Foodstuffs certified
Glove characteristics	Suitable for allergy sufferers
Glove characteristics	free of latex
Glove characteristics	Silicone-free
Protection class	Schutz gegen bakteriologische Risiken gemäß EN 374
EN 374:2016	Type A (AJKLOPT)
Resistance to chemicals	AJKLOPT
EN 388:2016	4001A
Material	Nitrile
Backing material	Nitril
AQL	0,65
Application range	All-round
Length	380 mm
Thickness	0.4 mm
Colour	black / green
Application	reusable
Weight	59 g
Cut protection class	A
Coating	Nitril
Type of product	Chemicals protection gloves