

uvex**Pair of chemical protective gloves uvex profabutyl B-05R, Glove size: 8****Order data**

Order number	094762 8
GTIN	4048612043097
Item class	04W

Description**Version:**

uvex profabutyl B-05R. Made of 100% butyl rubber, these gloves offer particular protection against esters and ketones. Highly impermeable to water vapour, gases and toxic chemicals. Temperature-resistant from approx. -20 °C to 90 °C.

Attention:

Butyl is not resistant to oils, greases, aliphatic and aromatic hydrocarbons, chlorinated hydrocarbons.

Note:

The minimum order quantity corresponds to one pack unit quantity (VPE) or a multiple thereof. EN 374:2016: Type A (ABIKLP)

Technical description

Glove size	8
Protection category	Category III
Type of glove	Chemicals protection gloves
Protection class	Schutz gegen bakteriologische Risiken gemäß EN 374

EN 374:2016	Type A (ABIKLP)
Resistance to chemicals	ABIKLP
EN 388:2016	2010X
Material	Butyl
Backing material	Butyl
Length	350 mm
Thickness	0.5 mm
Colour	black
Application	reusable
Contact heat up to	90 °C
Type of product	Chemicals protection gloves