

Ansell**Pair of cut-resistant heat resistant gloves HyFlex® 11-501, Glove size: 9****Order data**

Order number	094625 9
GTIN	10076490479869
Item class	04P

Description**Version:**

HyFlex® 11-501. Nitrile-coated **cut protection gloves** with additional protection against heat and molten metal spatter. **High mobility** due to Ansell Intercept Technology™. **Anti-static to EN 1149.**

Standard:

EN 388; EN 407; EN ISO 21420

Note:

The minimum order quantity corresponds to one pack unit quantity (VPE) or a multiple thereof.

Technical description

Glove size	9
Series	HyFlex®
Protection category	Category III
Type of glove	Heat protection gloves
Glove characteristics	Flame resistance stage X

Glove characteristics	free of latex
Glove characteristics	Silicone-free
EN 388	3X41D
EN 407	X1XXXX
Contact heat up to	100 °C
Backing material	Lycra®, Kevlar®
Coating	Nitrile foam
Coating variant	The palms of the hands
Colour	turquoise / grey
Material	Nitrile
Application	reusable
Length	206 mm
Contents	12
Washing	40 °C coloureds
Application range	All-round
Knitted technology	13G
Cut protection class	D
Standard	EN 407
Weight	25.9 g
Type of product	Heat protection gloves