

Ansell**Pair of cold protection gloves ActivArmr® 97-011, Glove size: 9****Order data**

Order number	094823 9
GTIN	76490457228
Item class	04P

Description**Version:**

ActivArmr® 97-011. Winter gloves with 3/4 nitrile coating resistant to the effects of wind, wetness and cold. **Good security of grip** due to rough coating. With **breathable double fabric** and **soft inner lining**.

Version of the advertising text:

ActivArmr® 97-011. Winter gloves with 3/4 nitrile coating resistant to the effects of wind, liquids and cold.

- **Good security of grip due to coating on the palm.**
- **Good visibility due to the orange backing material of acrylic polyester.**
- **With breathable double fabric and soft inner lining.**

Application:

For windy, cold or wet working conditions.

Use of the advertising text:

For windy, cold or wet working conditions.

Standard:

EN 388; EN 511

Note:

The minimum order quantity corresponds to one pack unit quantity (VPE) or a multiple thereof.

Note re advertising text:

The minimum order quantity corresponds to one pack unit quantity (VPE) or a multiple thereof.

Technical description

Glove size	9
Series	ActivArmr®
Type of glove	Cold protection gloves
Protection category	Category II
Contents	6
Application	reusable
Application range	All-round
Knitted technology	10G
Cut protection class	A
Length	240 mm
EN 388	4132A
EN 511	010
Backing material	Polyester acrylic
Material	Nitrile
Coating	Nitrile
Coating variant	3/4 coating
Colour	black / orange
Weight	72.1 g
Type of product	Cold protection gloves