

**Stepladder, double-sided access, Number of steps: 2X3****Order data**

Order number	966520 2X3
GTIN	4045197795922
Item class	92L

**Description****Version:**

Steps and stiles of aluminium with securely bolted step-stile connection, 80 mm deep serrated steps. Great stability due to robust construction. Non-slip end caps. Ladder inclination 20°. Step spacing 235 mm.

**Standard:**

**Gemäß DIN EN 131.**

**Technical description**

outer width at bottom	0.43 m
Accessibility	double-sided
Weight	4.4 kg
Working height approx.	2.25 m
Ladder length	0.69 m
Type of step	step

Length L	0.69 m
Ladders and platforms load capacity	150 kg
Type of product	Stepladder