

**Stepladder, double-sided access, Number of steps: 2X4****Order data**

Order number	966520 2X4
GTIN	4045197795939
Item class	92L

**Description****Version:**

Steps and stiles of aluminium with securely bolted step-stile connection, 80 mm deep serrated steps. Great stability due to robust construction. Non-slip end caps. Ladder inclination 20°. Step spacing 235 mm.

**Standard:**

**Gemäß DIN EN 131.**

**Technical description**

Ladder length	0.93 m
Weight	5.8 kg
Accessibility	double-sided
Working height approx.	2.5 m
outer width at bottom	0.46 m
Type of step	step

Length L	0.93 m
Ladders and platforms load capacity	150 kg
Type of product	Stepladder