



Stepladder, double-sided access, Number of steps: 2X5



Order data

Order number	966520 2X5
GTIN	4045197795946
Item class	92L

Description

Version:

Steps and stiles of aluminium with securely bolted step-stile connection, 80 mm deep serrated steps. Great stability due to robust construction. Non-slip end caps. Ladder inclination 20°. Step spacing 235 mm.

Standard:

Gemäß DIN EN 131.

Technical description

Ladder length	1.16 m
outer width at bottom	0.49 m
Weight	7.3 kg
Accessibility	double-sided
Working height approx.	2.75 m
Type of step	step

Length L	1.16 m
Ladders and platforms load capacity	150 kg
Type of product	Stepladder