



Try square Accuracy class 2, Stock length: 1000X500mm



Order data

Order number	452600 1000X500
GTIN	4045197205865
Item class	42F

Description

Version:

All faces and edges ground. Inspection test faces ground.

Application:

For accurate general workshop work.

Accuracy:

DIN 875 / 2 – angle tolerance e.g. for size 100×70 = 0.030 mm.

Standard: DIN 875

Right angle tolerance: 0.12 mm

Shank cross-section: 50×10 mm

Technical description

Right angle tolerance	0.12 mm
Shank cross-section	50×10 mm
Stock length	1000×500 mm
Standard	DIN 875
Accuracy	2

Type of product

Try squares

Services

Labelling laser-etched Type

018940