

HEDI

Cable drum plastic for F, B, PL and CZ, Type: 40B



Order data

Order number	081127 40B
GTIN	
Item class	08B

Description

Version:

Hedi® cable drums stand for “Made in Germany” quality and a long service life. The drum body is specially designed to optimally guide the cable. The integrated rotation stop switch prevents accidental drum rotation. All cable drums are equipped with thermal cut-out switches.

· **Overheating protection.**

With spring-loaded covers. For **continuous** use in the open air. Satisfies DGUV I 203-005 (formerly BGI 600).

PU armoured cable Plus.

Function:

IP44: Protected against splashed water from all directions and protected against penetration by foreign bodies with $\varnothing > 1$ mm, however tools and wires should be kept away.

Technical description

Material cable	Armoured cable
Cable length	40 m
Cable structure	3G1.5

IP Index of Protection	IP 44
Rated power unrolled	3500 (16 A) W
Cable class	H07BQ-F
Material of body	Plastic
Number of sockets	3
Power supply	Mains operated
Diagnostic system present	yes
Type of product	Cable drum