

HEDI

Cable drum plastic, Type: 25N



Order data

Order number	081125 25N
GTIN	4003644000074
Item class	08B

Description

Version:

Hedi® cable drums stand for “Made in Germany” quality and a long service life. The drum body is specially designed to optimally guide the cable. The integrated rotation stop switch prevents accidental drum rotation. All cable drums are equipped with thermal cut-out switches. With spring-loaded covers. For **continuous** use in the open air. Satisfies DGUV I 203-005 (formerly BGI 600).

Function:

IP44: Protected against splashed water from all directions and protected against penetration by foreign bodies with $\varnothing > 1$ mm, however tools and wires should be kept away.

IP Index of Protection: IP 44

impact-resistant and splash-proof: Category 2 (K2) to BGI

Rated power unrolled: 3500 (16A) W

Cable class: H07RN-F

Cable structure: 3G1.5

Material cable: Neoprene

Cable length: 25 m

Number of sockets: 3

Technical description

Cable structure	3G1.5
impact-resistant and splash-proof	Category 2 (K2) to BGI
Material cable	Neoprene
Cable length	25 m
Cable class	H07RN-F
Rated power unrolled	3500 (16A) W
IP Index of Protection	IP 44
Number of sockets	3
Material of body	Plastic
Power supply	Mains operated
Diagnostic system present	yes
Type of product	Cable drum