

HEDI**Cable drum plastic for F, B, PL and CZ, Type: 25N****Order data**

Order number	081127 25N
GTIN	4003644000067
Item class	08B

Description**Version:**

Hedi® cable drums stand for “Made in Germany” quality and a long service life. The drum body is specially designed to optimally guide the cable. The integrated rotation stop switch prevents accidental drum rotation. All cable drums are equipped with thermal cut-out switches.

• Overheating protection.

With spring-loaded covers. For **continuous** use in the open air. Satisfies DGUV I 203-005 (formerly BGI 600).

Function:

IP44: Protected against splashed water from all directions and protected against penetration by foreign bodies with $\varnothing > 1$ mm, however tools and wires should be kept away.

Technical description

Cable length	25 m
Cable structure	3G1.5
Cable class	H07RN-F
Rated power unrolled	3500 (16A) W

Material cable	Neoprene
IP Index of Protection	IP 44
impact-resistant and splash-proof	Category 2 (K2) to BGI
Number of sockets	3
Material of body	Plastic
Power supply	Mains operated
Diagnostic system present	yes
Type of product	Cable drum