



Socket set 1/2 inch square drive 31 pieces, Type: 12



Order data

Order number	638016 12
GTIN	4018754260881
Item class	63A

Description

Version:

Drives / accessories to DIN 3122 / 3123; sockets to DIN 3124. Internal / external square drives to **DIN 3120**. With bi-hexagon sockets No. 642100.

Application:

For hexagon head screws / nuts with thread M6 – M22 and hexagon socket head screws with thread M5 – M18.

Material:

Chrome alloy steel, chrome-plated.

Supplied with:

Sockets: 17 pcs. size 8; 10; 11; 12; 13; 14; 15; 16; 17; 18; 19; 21; 22; 24; 27; 30; 32 mm

Hexagon screwdriver bits: 8 pcs. No. 643200 size 4; 5; 6; 7; 8; 10; 12; 14

T-handle: 1 pc. No. 641300 size 300

Extensions: 3 pcs. No. 641000 75; 130; 255

Universal joint: 1 pc. No. 641600 size 1/2

Ratchet: 1 pc. No. 640100 size 1/2

Presented in: ABS plastic box

Height: 64 mm

Square drive: 1/2 inch

Width across flats range, bi-hex sockets: 8-32 mm

Width across flats range, hexagon wrenches: 4-14 mm

Technical description

Drive profile	Hexagon screwdriver
Drive profile	Bi-hex socket
Width across flats range, hexagon wrenches	4-14 mm
Width across flats	metric
Width across flats range, bi-hex sockets	8-32 mm
Number of pieces	31
Square drive	1/2 inch
Length	454 mm
Width	253 mm
Height	64 mm
Type of product	Socket spanner

Accessories

Hexagon screwdriver bit 1/2 inch Hexagon 6 mm	643200 6
Reversible ratchet, 1/2 inch Type	640100
Hexagon screwdriver bit 1/2 inch Hexagon 10 mm	643200 10
Hexagon screwdriver bit 1/2 inch Hexagon 7 mm	643200 7
Hexagon screwdriver bit 1/2 inch Hexagon 4 mm	643200 4
Extension, 1/2 inch overall length 75 mm	641000 75
Hexagon screwdriver bit 1/2 inch Hexagon 8 mm	643200 8
Hexagon screwdriver bit 1/2 inch Hexagon 12 mm	643200 12
Extension, 1/2 inch overall length 255 mm	641000 255
T-handle, 1/2 inch overall length 300 mm	641300 300
Hexagon screwdriver bit 1/2 inch Hexagon 14 mm	643200 14
Universal joint, 1/2 inch Type 1/2	641600 1/2
Hexagon screwdriver bit 1/2 inch Hexagon 5 mm	643200 5
Extension, 1/2 inch overall length 130 mm	641000 130