

**LED floodlight, 230 V, Power consumption: 26W****Order data**

Order number	081265 26
GTIN	5708997354407
Item class	08C

Description**Version:**

Sturdy LED floodlight with shock-resistant aluminium casing and rubber protective edge.

- **Soft non-shadowing anti-glare lamp, with low heat emission.**
- **High light output, low energy consumption, long working life.**
- **Certified for exterior use and for use in humid environments.**

NOVA work lamps with integral carrying handle. High-performance COB-LED with 5-step dimmer function, pivoting.

Function:

IP67: Protected against intermittent immersion in water and protected against penetration by dust (dust-tight), also completely protected against touching.

Technical description

Power consumption	29 W
Illumination	400 - 4000 lm
IP Index of Protection	IP 67
Light colour	6000 K

Weight	2380 g
Power supply	Mains-powered
Nominal voltage	100 - 240 V
Overall width	88 mm
Overall length	235 mm
Overall height	233 mm
Connection cable length	5 m
ATEX zone	no
Manufacturer's designation	NOVA 4K
Product name attribute	230 V
Type of product	Floodlight