

**LED floodlight, 230 V, Power consumption: 84W****Order data**

Order number	081265 84
GTIN	5708997354445
Item class	08C

Description**Version:**

Sturdy LED floodlight with shock-resistant aluminium casing and rubber protective edge.

- **Soft non-shadowing anti-glare lamp, with low heat emission.**
- **High light output, low energy consumption, long working life.**
- **Certified for exterior use and for use in humid environments.**

NOVA work lamps with integral carrying handle. High-performance COB-LED with 5-step dimmer function, pivoting.

Function:

IP67: Protected against intermittent immersion in water and protected against penetration by dust (dust-tight), also completely protected against touching.

Technical description

Light colour	6000 K
Power supply	Mains-powered
IP Index of Protection	IP 67
Illumination	1200 - 12000 lm

Power consumption	84 W
Weight	4100 g
Nominal voltage	100 - 240 V
Overall width	102 mm
Overall length	302 mm
Overall height	298 mm
Connection cable length	5 m
ATEX zone	no
Manufacturer's designation	NOVA 10K
Product name attribute	230 V
Type of product	Floodlight