

**LED floodlight, 230 V, Power consumption: 42W****Order data**

Order number	081265 42
GTIN	5708997354421
Item class	08C

**Description****Version:**

Sturdy LED floodlight with shock-resistant aluminium casing and rubber protective edge.

- **Soft non-shadowing anti-glare lamp, with low heat emission.**
- **High light output, low energy consumption, long working life.**
- **Certified for exterior use and for use in humid environments.**

**NOVA work lamps** with integral carrying handle. High-performance COB-LED with 5-step dimmer function, pivoting.

**Function:**

IP67: Protected against intermittent immersion in water and protected against penetration by dust (dust-tight), also completely protected against touching.

**Technical description**

Weight	2660 g
Power consumption	42 W
Light colour	6000 K
IP Index of Protection	IP 67

Illumination	600 - 6000 lm
Power supply	Mains-powered
Nominal voltage	100 - 240 V
Overall length	267 mm
Overall width	87 mm
Overall height	262 mm
Connection cable length	5 m
ATEX zone	no
Manufacturer's designation	NOVA 6K
Product name attribute	230 V
Type of product	Floodlight