



LED cordless work lamp, Type: 26



Order data

Order number	081254 26
GTIN	5708997354414
Item class	08C

Description

Version:

Sturdy LED floodlight with shock-resistant aluminium casing and rubber protective edge.

- **Soft non-shadowing anti-glare lamp, with low heat emission.**
- **High light output, low energy consumption, long working life.**
- **Certified for exterior use and for use in humid environments.**

NOVA work lamps with integral carrying handle. High-performance COB-LED with 5-step dimmer function, pivoting. Due to the dual system, can be used both as a mobile cordless floodlight, and also with mains cable. Charge status display, remaining time display, dimmable in 5 stages.

Function:

IP67: Protected against intermittent immersion in water and protected against penetration by dust (dust-tight), also completely protected against touching.

Supplied with:

Including battery charger.

Technical description

Illumination	400 - 4000 lm
IP Index of Protection	IP 67

Power supply	Rechargeable battery-powered
Illumination time	1 - 14 h
ATEX zone	no
Colour temperature	6000 K
Battery voltage	11.1 V
Type of rechargeable battery	Lithium-ion
Battery capacity	4.4 Ah
Number of rechargeable batteries contained	1
Overall length	235 mm
Overall height	233 mm
Overall width	88 mm
CRI value	80
Weight	1780 g
Power consumption	29 W
Manufacturer's designation	NOVA 3K C+R
Type of product	Work lamp

Accessories

Li-ion battery Battery capacity 4400 mAh	081431 4400
--	-------------