

**LED cordless floodlight, Power consumption: 18W****Order data**

Order number	081266 18
GTIN	5708997354513
Item class	08C

Description**Version:**

Non-shadowing and non-dazzle version with wide spread of light.
With 2 lighting levels and up to 3 hours illumination. Base of steel, powder-coated.

Function:

IP54: Protected against splashed water from all directions and protected against penetration of dust into the inside (protected against dust), also completely protected against touching.

Suitable for:

Three-leg stand No. 081252 size 1.35-3.

Technical description

Number of rechargeable batteries contained	1
Power supply	Rechargeable battery-powered
Illumination	2500 lm
IP Index of Protection	IP 54
Colour temperature	6500 K
ATEX zone	no

Battery voltage	11.1 V
Illumination time	3 h
Battery capacity	2.6 Ah
Type of rechargeable battery	Lithium-ion
Overall height	280 mm
Overall width	103 mm
Overall length	288 mm
Illumination step 2	750 lm
CRI value	80
Weight	1600 g
Manufacturer's designation	VEGA 1500 C+R
Type of product	Area light