

**KERN**
**Platform scales, type DS high resolution, maximum weighing range: 36kg**


## Order data

Order number	479610 36
GTIN	4045761096233
Item class	47D

## Description

### Version:

- **Robust platform scales can be used as parcel, industrial, and counting scales.**
- **Display unit with numeral height 18 mm can be remote from platform; can be stood or mounted using flexible cable.**
- **Robust platform with a protective hood over the display unit.**
- **Simple, self-explanatory user guidance with (yes/no) dialogue in the display.**
- **Selectable mains or battery operation (battery available on request).**
- **Units of weight (e. g. screw weight) can be freely programmed.**
- **With automatic reference optimisation for exact counting.**
- **CAL calibration programme: For setting the accuracy (external calibration weight required for this available on request).**
- **Quantity counting: Reference quantities selectable 1, 5, 10, 20 pieces.**
- **Display selectable between pieces and weight.**
- **Numeric tare preference for well-known container weight. Useful for filling quantities.**
- **Percentage determination: Display of deviation from the reference weight in % instead of in grams.**

### Supplied with:

Mains adapter 230 V / 50 Hz and protective hood.

### Optional extras:

Internal and external battery, calibration weight, wall bracket, printer and stand available on request.

Interface: RS232C interface  
 Calibration: Price on request  
 Scale divisions: 0.2 g  
 Reproducibility: 0.2 g  
 Settling time: 3 s  
 Minimum unit weight: 2 g  
 Dimensions of weighing plate: 308×318 mm  
 Net weight: 7.5 kg

## Technical description

Net weight	7.5 kg
Reproducibility	0.2 g
maximum weighing range	0 - 36 kg
Settling time	3 s
Scale divisions	0.2 g
Manufacturer's designation	DS
Calibration	Price on request
Minimum unit weight	2 g
Dimensions of weighing plate	308×318 mm
Series	DS
Power supply	Mains-powered
Power supply	Mains operated
Article no of the battery / rechargeable battery fitted	0
Nominal voltage	230 V
Number height display unit	18 mm
Interface	RS232C interface
Type of product	Platform balance

## Services

Labelling laser-etched Type	018940
Calibration Scales maximum weighing range 50 kg	027700 50

