

KERN**Platform scales, type DS high resolution, maximum weighing range: 150kg**

Order data

Order number	479610 150
GTIN	4045761096257
Item class	47D

Description

Version:

- **Robust platform scales can be used as parcel, industrial, and counting scales.**
- **Display unit with numeral height 18 mm can be remote from platform; can be stood or mounted using flexible cable.**
- **Robust platform with a protective hood over the display unit.**
- **Simple, self-explanatory user guidance with (yes/no) dialogue in the display.**
- **Selectable mains or battery operation (battery available on request).**
- **Units of weight (e. g. screw weight) can be freely programmed.**
- **With automatic reference optimisation for exact counting.**
- **CAL calibration programme: For setting the accuracy (external calibration weight required for this available on request).**
- **Quantity counting: Reference quantities selectable 1, 5, 10, 20 pieces.**
- **Display selectable between pieces and weight.**
- **Numeric tare preference for well-known container weight. Useful for filling quantities.**
- **Percentage determination: Display of deviation from the reference weight in % instead of in grams.**

Supplied with:

Mains adapter 230 V / 50 Hz and protective hood.

Optional extras:

Internal and external battery, calibration weight, wall bracket, printer and stand available on request.

Technical description

Dimensions of weighing plate	450x350 mm
Manufacturer's designation	DS
Reproducibility	1 g
Settling time	3 s
Calibration	Price on request
Minimum unit weight	10 g
Scale divisions	1 g
maximum weighing range	0 - 150 kg
Net weight	9.5 kg
Series	DS
Power supply	Mains-powered
Power supply	Mains operated
Nominal voltage	230 V
Number height display unit	18 mm
Interface	RS232C interface
Type of product	Platform balance

Services

CalibrationScales maximum weighing range 150 kg	027700 150
DAkkS calibrationScales maximum weighing range 180	027710 180