

**LED cordless floodlight, Power consumption: 20****Order data**

Order number	081286 20
GTIN	4045197796295
Item class	02A

**Description****Version:**

Sturdy LED floodlight with shock-resistant aluminium casing and rubber protective edge.

- **Soft non-shadowing anti-glare lamp, with low heat emission.**
- **High light output, low energy consumption.**
- **Certified for exterior use and for use in humid environments.**

SMD-LED work lights with frosted glass lens for homogeneous and pleasant illumination.

**Function:**

IP65: Protected against jets of water from all directions and protected against penetration by dust (dust-tight), also completely protected against touching.

**Supplied with:**

Including battery charger.

**Technical description**

Type of rechargeable battery	Lithium-ion
Illumination	1600 lm
ATEX zone	no
IP Index of Protection	IP 65



Battery voltage	7.4 V
Battery capacity	8 Ah
Illumination time	3 h
Power supply	Rechargeable battery-powered
Number of rechargeable batteries contained	1
Overall length	202 mm
Overall height	202 mm
Overall width	55 mm
Weight	1450 g
Power consumption	20 W
Type of product	Work lamp