

**LED floodlight, 230 V, Power consumption: 60W****Order data**

Order number	081287 60
GTIN	4045197796400
Item class	02A

Description**Version:**

SMD-LED work lights with frosted glass lens for homogeneous and pleasant illumination and two splash-proof sockets.

Sturdy LED floodlight with shock-resistant aluminium casing and rubber protective edge.

- **Soft non-shadowing anti-glare lamp, with low heat emission.**
- **High light output, low energy consumption.**
- **Certified for exterior use and for use in humid environments.**
- **Soft non-shadowing anti-glare lamp, with low heat emission.**
- **High light output, low energy consumption, long working life.**
- **Certified for exterior use and for use in humid environments.**

With **2 splash-proof sockets.**

Function:

IP54: Protected against splashed water from all directions and protected against penetration of dust into the inside (protected against dust), also completely protected against touching.

Technical description

Weight	3330 g
Power consumption	60 W

Power supply	Mains-powered
Illumination	2250 - 4500 lm
IP Index of Protection	IP 54
Nominal voltage	230 V
Overall width	292 mm
Overall length	292 mm
Overall height	80 mm
Connection cable length	5 m
ATEX zone	no
Product name attribute	230 V
Type of product	Floodlight