

3M**Fleece finishing belt (A) SC-BS, 30×533 mm, Grit equivalent: 180****Order data**

Order number	558498 180
GTIN	4001895541582
Item class	53M

Description**Version:**

Synthetic nylon non-woven fabric with synthetic resin bonded abrasive grit, long service life, **consistent surface finish, low heat generation.**

Flexible fleece belt for use on hand-held machines.

Application:

For rubbing down rough ground or brushed surfaces, for consistent and reproducible results. Also suitable for removing rust film, light soiling, and discolouration.

Technical description

Colour	red
Version	A medium
Grit equivalent	180
Grit designation	medium
Series	SC-BS
Grinding medium code	A

Iron, sulphur and chlorine constituents	< 0.1 %
Linishing belt width	30 mm
Linishing belt length	533 mm
Product name attribute	30×533 mm
Type of product	Fleece linishing belt

User data

	Suitability	V _c	ISO code
Alu Mg	suitable only under restricted conditions	15-20 m/s	
Steel < 900 N/mm ²	suitable	10 m/s	P
Steel < 1400 N/mm ²	suitable	10 m/s	P
Steel < 55 HRC	suitable	10 m/s	H
Steel < 60 HRC	suitable	10 m/s	H
Steel < 67 HRC	suitable	10 m/s	H
INOX	suitable	10 m/s	
Ti	suitable	10 m/s	
GG(G)	suitable	10 m/s	K
CuZn	suitable	10 m/s	N
Plastic, GRP	suitable	10 m/s	
Wood	suitable	10 m/s	
Paint	suitable	10 m/s	
Uni	suitable	10 m/s	
dry	suitable		