



XT internal micrometer, Measuring range: 2,5-3mm



Order data

Order number	428500 2,5-3
GTIN	2050001893055
Item class	46B

Description

Version:

3-Point **XT inside micrometers**. Measuring spindle hardened and ground. Micrometer barrel with black scale, all reading parts satin chrome-plated. Ratchet for consistent measuring force. All gauges supplied with serial number and test certificate. "Micro" - version with better resolution of 2 µm.

Application:

Blind holes and through holes, centring edges.

Optional extras:

Setting rings No. 484030, extension No. 428510.

Spare part:

Micrometer heads No. 428605.

Attention:

XT internal micrometer for **2-point measurement**.

Technical description

Scale divisions	0.002 mm
Error limit	0.004 mm
Dimension a	0 mm
Standard measuring depth	9 mm
Standard	DIN 863
Micrometer barrel graduations	1/50 mm

Measurement technology	analogue
Packaging	sturdy box
Calibration	B6
Type of product	3-point internal micrometer

Services

Calibration3-point internal micrometer maximum measuring range 20 mm	022500 20
DAkkS calibration3-point internal micrometer maximum measuring range 200 mm	022510 200

Accessories

Setting ringDIN 2250 C Nominal size \varnothing 3 mm	484030 3
--	----------