



## XT internal micrometer, Measuring range: 2-2,5mm



### Order data

Order number	428500 2-2,5
GTIN	2050001893048
Item class	46B

### Description

#### Version:

3-Point **XT inside micrometers**. Measuring spindle hardened and ground. Micrometer barrel with black scale, all reading parts satin chrome-plated. Ratchet for consistent measuring force. All gauges supplied with serial number and test certificate. "Micro" - version with better resolution of 2  $\mu\text{m}$ .

#### Application:

Blind holes and through holes, centring edges.

#### Optional extras:

Setting rings No. 484030, extension No. 428510.

#### Spare part:

Micrometer heads No. 428605.

#### Attention:

XT internal micrometer for **2-point measurement**.

### Technical description

Scale divisions	0.002 mm
Dimension a	0 mm
Standard measuring depth	9 mm
Error limit	0.004 mm
Standard	DIN 863
Micrometer barrel graduations	1/50 mm

Measurement technology	analogue
Packaging	sturdy box
Calibration	B6
Type of product	3-point internal micrometer

## Services

DAkkS calibration3-point internal micrometer maximum measuring range 200 mm	022510 200
Calibration3-point internal micrometer maximum measuring range 20 mm	022500 20