



## XT internal micrometer set, Measuring range: 2-3mm



### Order data

|              |               |
|--------------|---------------|
| Order number | 428550 2-3    |
| GTIN         | 5051102212063 |
| Item class   | 46B           |

### Description

#### Version:

3-Point **XT inside micrometers**. Measuring spindle hardened and ground. Micrometer barrel with black scale, all reading parts satin chrome-plated. Ratchet for consistent measuring force. All gauges supplied with serial number and test certificate. "Micro" - version with better resolution of 2  $\mu\text{m}$ .

#### Application:

Blind holes and through holes, centring edges.

#### Supplied with:

Internal micrometers No. 428500 and setting rings with UKAS test certificate.

#### Optional extras:

Setting rings No. 484030, extension No. 428510.

#### Spare part:

Micrometer heads No. 428605.

#### Attention:

XT internal micrometer set for **2-point measurement**.

### Technical description

|                         |   |
|-------------------------|---|
| Number of micrometers   | 2 |
| Number of setting rings | 1 |

|                               |                             |
|-------------------------------|-----------------------------|
| Setting ring Ø                | 2.5 mm                      |
| Standard                      | DIN 863                     |
| Micrometer barrel graduations | 1/50 mm                     |
| Measurement technology        | analogue                    |
| Packaging                     | sturdy box                  |
| Calibration                   | S6                          |
| Type of product               | 3-point internal micrometer |

### Services

|   |            |
|---|------------|
| CalibrationInternal micrometer set Measuring range 2-6 mm | 020550 2-6 |
|---|------------|

### Accessories

|   |              |
|---|--------------|
| XT internal micrometer Measuring range 2,5-3 mm | 428500 2,5-3 |
| XT internal micrometer Measuring range 2-2,5 mm | 428500 2-2,5 |
| Setting ringDIN 2250 C Nominal size Ø 3 mm      | 484030 3     |