



XT internal micrometer set, Measuring range: 3-6mm



Order data

Order number	428550 3-6
GTIN	5051102212087
Item class	46B

Description

Version:

3-Point **XT inside micrometers**. Measuring spindle hardened and ground. Micrometer barrel with black scale, all reading parts satin chrome-plated. Ratchet for consistent measuring force. All gauges supplied with serial number and test certificate. "Micro" - version with better resolution of 2 μm .

Application:

Blind holes and through holes, centring edges.

Supplied with:

Internal micrometers No. 428500 and setting rings with UKAS test certificate.

Optional extras:

Setting rings No. 484030, extension No. 428510.

Spare part:

Micrometer heads No. 428605.

Attention:

XT internal micrometer set for **2-point measurement**.

Technical description

Setting ring \varnothing	4 / 5 mm
Number of micrometers	3

Number of setting rings	2
Standard	DIN 863
Micrometer barrel graduations	1/50 mm
Measurement technology	analogue
Packaging	sturdy box
Calibration	S6
Type of product	3-point internal micrometer

Services

CalibrationInternal micrometer set Measuring range 2-6 mm	020550 2-6
---	------------

Accessories

Setting ringDIN 2250 C Nominal size Ø 4 mm	484030 4
Setting ringDIN 2250 C Nominal size Ø 6 mm	484030 6
Setting ringDIN 2250 C Nominal size Ø 5 mm	484030 5
XT internal micrometer Measuring range 3-4 mm	428500 3-4
XT internal micrometer Measuring range 4-5 mm	428500 4-5
XT internal micrometer Measuring range 5-6 mm	428500 5-6