


Boring bar head for radial turrets, Type C H = 150, Clamping Ø: 32 mm



Order data

Order number	319174 32
GTIN	4251414900714
Item class	38T

Description

Version:

The first successful introduction of a tool mounting design which can be used on both disc turrets and radial turrets. Irrespective of the alignment method in use.

Modular system configuration.

Advantage:

- **All tools with direct internal coolant supply connection.**
- **Cost reduction via efficient stock-holding of bearings.**
- **Higher productivity due to improved positioning.**

Application:

Can be inserted by changing over the locking cover.

Note:

Suitable for vibration-damped boring bars No. 264902 – 264908, No. 264910 – 264922 or tools with plain shank (such as: solid carbide boring bars Ø 10 mm).

Length L: 128 mm

Technical description

Clamping Ø	32 mm
Length L	128 mm
Adapter	Type C H = 150

