

## Individual stainless steel test pin Tolerance class 1, Type: 3



### Order data

Order number	483914 3
GTIN	2050001864192
Item class	48A

### Description

**IMPORTANT: item is configurable**

Nominal size: 3 - 5.99 mm, Intervall: 0,010

**Version:**

Test pin of stainless and acid-resistant material, hardened (58-62 HRC) and tempered. Surface ground and lapped. From  $\varnothing$  1.50 the dimension is marked on the sleeve; from  $\varnothing$  3.00 on the end face. From  $\varnothing$  1.00 mm, one end chamfered.

**Note:**

When ordering, **please additionally state the desired  $\varnothing$** , e.g. No. 483914 size 5 **10.08**.

Calibration: L5

Nominal size: 3 - 5.99 mm

Pitch: 0.01 mm

Gauging pin length: 70 mm

### Technical description

Pitch	0.01 mm
Gauging pin length	70 mm
Nominal size	3 - 5.99 mm
Standard	DIN 2269
Calibration	L5
Type of product	Test pin

### Services

Calibration Test pin Type	018380
DAkkS calibration Test pin Type	018650
Calibration Test pin maximum Ø 20	028240 20
DAkkS calibration Test pin maximum Ø 20	028260 20
Labelling laser-etched Type	018940