

Individual stainless steel test pin Tolerance class 1, Type: 4



Order data

Order number	483914 4
GTIN	2050001864062
Item class	48A

Description

IMPORTANT: item is configurable

Nominal size: 6 - 9.99 mm, Intervall: 0,010

Version:

Test pin of stainless and acid-resistant material, hardened (58-62 HRC) and tempered. Surface ground and lapped. From \varnothing 1.50 the dimension is marked on the sleeve; from \varnothing 3.00 on the end face. From \varnothing 1.00 mm, one end chamfered.

Note:

When ordering, **please additionally state the desired \varnothing** , e.g. No. 483914 size 5 **10.08**.

Calibration: L5

Nominal size: 6 - 9.99 mm

Pitch: 0.01 mm

Gauging pin length: 70 mm

Technical description

Pitch	0.01 mm
Gauging pin length	70 mm
Nominal size	6 - 9.99 mm
Standard	DIN 2269
Calibration	L5
Type of product	Test pin

Services

Calibration Test pin Type	018380
DAkkS calibration Test pin Type	018650
Calibration Test pin maximum Ø 20	028240 20
DAkkS calibration Test pin maximum Ø 20	028260 20
Labelling laser-etched Type	018940