



Spanner bit 1/4 inch C 6.3, Type: 4



Order data

Order number	675395 4
GTIN	4013288038609
Item class	63H

Description

Version:

For use in manual drivers or machines with suitable hexagon holder or for use in adapters No. 675000 – 675050.

Standard design, **high strength**.

Application:

For clamping screws (snake eyes)

Standard:

DIN ISO 1173.

Material:

Chrome vanadium special alloy, **high strength**.

Technical description

Clamp profile	4
overall length	25 mm
Bit hexagon shank	C 6,3
Pin spacing	1.52 mm
Manufacturer's designation	857/1 Z Spanner
Drive profile	Clamp insert
Type of product	Bit tool

