



Tool24 Smartline – cabinet system including dividing material, Type: S11M



Order data

Order number	979000 S11M
GTIN	4045197815323
Item class	9SA

Description

Version:

Flexible goods issuing system for storage and management of machining and assembly tools, measuring tools, protective work-wear and many other consumable items. Master systems can be extended using the optional extension cabinets (slave system). The individual software packages allow the systems to be tailored to your exact requirements.

Body and doors made of 1 mm sheet metal. Pallet truck base made of 1.75 mm sheet metal. Storage shelf made of bamboo

Application:

Automatic goods issuing system for storage and management of tools and accessories.

Content:

Divider: 10× 960310_4+18; 1×960330_3+14

Components:

Number of drawers × drawer front height: 1 technical drawer
10×75 mm; 1×150 mm

Supplied with:

Master system: Tool issuing cabinet with 11 drawers 36×36 U, touch screen, barcode scanner, PC including BASIC software package and dividers.

Supplied with:

Touch screen 22 inch, barcode scanner, PC including BASIC software package

Colour:

Body RAL 7035 light grey, drawers RAL 5005 signal blue, **powder-coated.**

Colour selection: RAL 9002, 7035, 7005, 7016, 6011, 5018, 5012, 5011, 5005, 3003

Drawer/pull-out shelf load capacity: 75 kg

Storage area: 4 m²

Height: 1390 mm

Width: 717 mm

Depth: 750 mm

Drawer usable width: 612 mm

Drawer usable depth: 612 mm

Technical description

Storage area	4 m ²
Division within a drawer	36×36 U
Height	1390 mm
Number of drawers	11
Drawer usable width	612 mm
Weight	249 kg
Width	717 mm
Depth	750 mm
Drawer usable depth	612 mm
Type	Basic master cabinet, complete
Drawer/pull-out shelf load capacity	75 kg
Drawer runner extension	Anti-tilt lock
Colour selection	RAL 9002, 7035, 7005, 7016, 6011, 5018, 5012, 5011, 5005, 3003
Type of product	Tool issuing system