



Hinged pin wrench offset, largest \varnothing / pin nominal \varnothing : 80/4mm



Order data

| | |
|--------------|---------------|
| Order number | 628810 80/4 |
| GTIN | 4020772051075 |
| Item class | 63Q |

Description

Version:

Special steel, drive head ground, annealed and burnished.
Cranked, with interchangeable pins.

Application:

For twin hole nuts.

Note:

Pin \varnothing = pin nominal \varnothing - 0.1 mm; tolerance field h12.

Technical description

| | |
|----------------------------|-------------|
| Pin spacing adjustable a | 40 - 80 mm |
| overall length | 215 mm |
| Pin nominal \varnothing | 4 mm |
| largest \varnothing | 80 mm |
| Type | 764C |
| Pin thread | M6 |
| Manufacturer's designation | 764CC |
| Type of product | Pin spanner |

Accessories

Sorting box, 20 pieces, with loose pins and nuts.

628850