



Hinged pin wrench offset, largest \varnothing / pin nominal \varnothing : 80/5mm



Order data

Order number	628810 80/5
GTIN	4020772051082
Item class	63Q

Description

Version:

Special steel, drive head ground, annealed and burnished.
Cranked, with interchangeable pins.

Application:

For twin hole nuts.

Note:

Pin \varnothing = pin nominal \varnothing - 0.1 mm; tolerance field h12.

Technical description

largest \varnothing	80 mm
Pin spacing adjustable a	40 - 80 mm
overall length	215 mm
Pin nominal \varnothing	5 mm
Type	764C
Pin thread	M6
Manufacturer's designation	764CC
Type of product	Pin spanner

Accessories

Sorting box, 20 pieces, with loose pins and nuts.

628850