



Circular saw blade expert for Stainless Steel, Blade Ø D: 355mm



Order data

Order number	583900 355
GTIN	3165140839983
Item class	54B

Description

Version:

Precision saw blade with high-strength, **noise and vibration suppressing blade body**. The tensioning ring incorporated ensure stability of the shape in all temperature ranges. The **coating** prevents adhesions, keeps the saw blade cool and protects it against corrosion. **Precision-ground carbide teeth** ensure a long working life and best quality of cut.

Application:

For **machining stainless steel**. Saw teeth of **Cermet** with particularly high hardness and wear resistance. Unsuitable for high-alloy steels. Tooth form: Trapezoidal flat teeth, neutral rake angle. For tenon saws and mitre saws.

Note:

Further circular saw blades can be found in Group 17.

Technical description

Bore Ø	25.4 mm
Ø	355 mm
Number of teeth	90

Width of cut B	2.5 mm
Type of product	Circular saw blade