

**Circular saw blade expert for Aluminium, Blade Ø D: 165mm****Order data**

Order number	583920 165
GTIN	3165140796613
Item class	54B

Description**Version:**

Precision saw blade with high-strength, **noise and vibration suppressing blade body**. The tensioning ring incorporated ensure stability of the shape in all temperature ranges. The **coating** prevents adhesions, keeps the saw blade cool and protects it against corrosion. **Precision-ground carbide teeth** ensure a long working life and best quality of cut.

Application:

Precise cutting in **aluminium** and other non-ferrous metals. Tooth form: Trapezoidal flat teeth with negative rake angle for easy and safe working with manual infeed. For plunge-cut and portable circular saws.

Note:

Further circular saw blades can be found in Group 17.

Technical description

Ø	165 mm
Bore Ø	20 mm
Number of teeth	52

Width of cut B	2.6 mm
Drive holes number/Ø/pitch circle	2/6/32.5 mm
Type of product	Circular saw blade