



## Circular saw blade expert for Aluminium, Blade Ø D: 254mm



### Order data

Order number	583920 254
GTIN	3165140796781
Item class	54B

### Description

#### Version:

Precision saw blade with high-strength, **noise and vibration suppressing blade body**. The tensioning ring incorporated ensure stability of the shape in all temperature ranges. The **coating** prevents adhesions, keeps the saw blade cool and protects it against corrosion. **Precision-ground carbide teeth** ensure a long working life and best quality of cut.

#### Application:

Precise cutting in **aluminium** and other non-ferrous metals. Tooth form: Trapezoidal flat teeth with negative rake angle for easy and safe working with manual infeed. For tenon saws and mitre saws, panel saws.

#### Note:

**Further circular saw blades can be found in Group 17.**

### Technical description

Bore Ø	30 mm
Ø	254 mm
Number of teeth	80

Width of cut B	2.8 mm
Drive holes number/Ø/pitch circle	2/7/42 and 2/9.5/46.5 and 2/9/46 and 2/10/60 mm
Type of product	Circular saw blade