

**Circular saw blade expert for multi-material, Blade Ø D: 216mm****Order data**

Order number	583930 216
GTIN	3165140648189
Item class	54B

**Description****Version:**

Precision saw blade with high-strength, **noise and vibration suppressing blade body**. The tensioning ring incorporated ensure stability of the shape in all temperature ranges. The **coating** prevents adhesions, keeps the saw blade cool and protects it against corrosion. **Precision-ground carbide teeth** ensure a long working life and best quality of cut.

**Application:**

For cutting **various materials** such as laminated boards, epoxy, wood and non-ferrous metals. Tooth form: Trapezoidal flat teeth, negative rake angle. For bench circular saws, tenon saws and mitre saws, panel saws.

**Note:**

**Further circular saw blades can be found in Group 17.**

**Technical description**

Bore Ø	30 mm
Ø	216 mm
Number of teeth	64

Width of cut B	2.4 mm
Type of product	Circular saw blade