

Garant**Centring vice, pneumatic, Type: 160****Order data**

Order number	360180 160
GTIN	4062406198732
Item class	310

Description**Version:**

- **Adjustable stroke + 5 mm per end.**
- **Clamping force steplessly adjustable up to 22.5 kN. Arithmetical sum = 45 kN.**
- **Even if the compressed air supply fails, the centring vice maintains a slight (approx. 60 kg) pre-load, to ensure secure positioning of the workpiece, such as when a shuttle table is being used.**

Application:

For centralised clamping of components. Suitable for **automated operation** with 4-channel clamping pots, even with side connections.

Optional extras:

Range of jaws no. 360183 - 360187.

Technical description

Weight	12.2 kg
Height H	99.2 mm
Clamping force up to maximum	22.5 kN
L	160 mm

B	160 mm
Maximum compressed air supply	9 bar
Clamping range	8.5 mm
Jaw width A	104 mm
suitable for colour code	PCV 160
Type of product	Machine vice