

HOLEX**Abrasive flap disc speed ZA, flat, Ø 125 mm, Grit: 40****Order data**

| | |
|--------------|---------------|
| Order number | GG5295 40 |
| GTIN | 4062406201746 |
| Item class | GGN |

Description**Version:**

- **High-quality zirconium aluminium oxide (ZA) for high abrasive performance.**
- **Glass fibre pad for optimum contact pressure.**
- **Suitable for both steel and stainless steel.**
- **Best results on angle grinders of all power classes.**

speed - flat flap strip arrangement, for **high metal removal rate** and long tool life.

Corresponds to 565295

Application:

Precise chamfering, edge smoothing and surface abrasion.

Note:

Only sold in bulk pack quantities, not supplied individually. Ordering information: 1 set = 1 bulk pack.

Technical description

| | |
|--------|----------|
| Bore Ø | 22.23 mm |
| Disc Ø | 125 mm |

| | |
|---|-------------------------|
| Shape description | flat |
| Contents | 100 |
| Grinding media | Zirconium abrasive (ZA) |
| Grinding medium code | ZA |
| Iron, sulphur and chlorine constituents | < 0.1 % |
| Product name attribute | Ø 125 mm |
| optimised for material | INOX |
| optimised for material | Steel |
| maximum circumferential speed | 80 m/s |
| Type of product | Abrasive flap disc |

User data

| | Suitability | V _c | ISO code |
|--------------------------------|---|----------------|----------|
| Steel < 900 N/mm ² | suitable | | |
| Steel < 1400 N/mm ² | suitable | | |
| Steel < 55 HRC | suitable | | |
| Steel < 60 HRC | suitable | | |
| Steel < 67 HRC | suitable | | |
| INOX | suitable | | |
| Ti | suitable only under restricted conditions | | |
| GG(G) | suitable only under restricted conditions | | |
| Uni | suitable | | |
| dry | suitable | | |

Accessories

| | |
|--|-----------|
| Abrasive flap discspeed ZA, flat Grit 40 | 565295 40 |
|--|-----------|