


**Velour-backed abrasive disc (A) 15 holes, Ø 150 mm, Grit: 100****Order data**

Order number	GG5779 100
GTIN	4062406201807
Item class	GGN

Description**Version:**

Dust-repellent coating prevents premature clogging. The back is covered with hook and loop backing.

Velour-backed abrasive disc with semi-open distribution, aluminium oxide (A).

Corresponds to 567790.

Application:

On **orbital sanders** with hook and loop pads e.g.No. 567990 (dust extraction available).

Universal **all-round product** for coarse, intermediate and fine abrasion on all metal and plastic surfaces, paint systems and woods.

Universal **all-round product** for coarse, intermediate and fine abrasion on all metal and plastic surfaces, paint systems and woods.

Technical description

Disc Ø	150 mm
Grit	100
Contents	500

Grinding medium code	A
Iron, sulphur and chlorine constituents	< 0.1 %
Product name attribute	Ø 150 mm
Number of dust extraction holes	15
Propulsive equipment	Orbital sander
maximum circumferential speed	40 m/s
Type of product	Velour-backed abrasive disc

User data

	Suitability	V _c	ISO code
Alu Mg	suitable		
Steel < 900 N/mm ²	suitable		
Steel < 1400 N/mm ²	suitable		
Steel < 55 HRC	suitable		
Steel < 60 HRC	suitable		
Steel < 67 HRC	suitable only under restricted conditions		
INOX	suitable		
Ti	suitable only under restricted conditions		
CuZn	suitable		
Plastic, GRP	suitable		
Wood	suitable		
Paint	suitable		
Uni	suitable		
dry	suitable		

Accessories

PU hook and loop backing pad External Ø 150 mm	567885 150
--	------------

PU hook and loop backing pad Multiple holes Outer Ø 150 mm	567887 150
Multi-hole PU backing pad External Ø 147 mm	567990 147
Velour-backed abrasive disc (A) 15 holes Grit 100	567790 100